

Product sheet



LEGRAND

Stabilised mono switching power supply - 20-60 W - output 12 V= - 40 W

REF. 146602 | EAN. 3414970543134

> [Visit e-catalogue](#)

Product characteristics

- Stabilised switched mode power supplies - single-phase - Conforming to standards UL 508, IEC EN 60950 - 1 and IEC EN 61204 - 3 - UL - approved in USA and Canada - Operating frequency : 50/60 Hz - Output voltage present indicator - Potentiometer for adjusting the output voltage on front panel - With signal or relay contact for feedback on the status of the active output voltage (except 75 W) - Connection with copper conductors only - For mounting on a symmetrical rail depth 7.5 mm and 15 mm
- Single-phase 20 - 60 W - No - load power consumption - Adjustable output voltage - Plastic casingInput voltage : 100 to 240 V~ Output voltage : 12 V= - Nominal power : 40 W - Nominal rating : 3.33 A - Setting range : 12 to 15 V - Width : 40 mm

Documentation

TECHNICAL DOCUMENTATION

-  F02123EN-00.pdf | PDF (0.7Mo)
-  LE07893AA-01.pdf | PDF (0.46Mo)
-  F02123FR-00.pdf | PDF (0.71Mo)

CAD & Design specs / BIM

-  146602.dwg | DWG (0.07Mo)

CATALOGUE PAGE & OTHERS

-  ex223001_0509.pdf | PDF (0.03Mo)
-  ex223001_0505.pdf | PDF (0.25Mo)
-  ex223001_0507.pdf | PDF (0.06Mo)
-  ex223001_0510.pdf | PDF (0.03Mo)

Agreements & Certificates

-  UL listed cULus-E223674 | (0.04Mo)