

Product sheet



LCS³ LEGRAND

RJ45 field plug to be crimped Category 6 UTP

REF. 051710 | EAN. 3414972093903

> [Visit e-catalogue](#)

Product characteristics

- Category 6 UTP : for up to 1 Gigabit per second data rate, unshielded.
- 0,5 µinch gold - plated contact
- Fire resistance UL 94 V2
- Compatible remote powering PoE up to 100W
- Transparent polycarbonate body

Recommendation / Restriction

- Inserting an uncrimped plug in an RJ socket risks damaging both the plug and socket contacts. When making a Category 5E or 6 connection, the minimum pairuntwisting distance should be kept between conductors. Use RJ crimping tool ref. 051709 to ensure good connection.

The product's benefits

Installation


- Cabling standard : TIA 568A ans 568B


Usage

- RJ45 plug can be covered with a white protective sleeve ref. 051706 or black ref. 051707


Documentation

TECHNICAL DOCUMENTATION

 S000100326EN-03.pdf | PDF (0.45Mo)

 S000100326FR-03.pdf | PDF (0.49Mo)

Agreements & Certificates

 LGRP-01405-V01.01-EN.PDF | PDF (0.83Mo)

CATALOGUE PAGE & OTHERS

 ex223001_0996.pdf | PDF (0.09Mo)