

Product sheet



LEGRAND

Add-on modules DX³ - 2P 230 V~ - 40 A - 30 mA - A type - for 1 module DX³ MCB

REF. 410428 | EAN. 3245064104289

> [Visit e-catalogue](#)

Product characteristics

- Add - on modules DX³ - for 1 module/pole DX³ MCBs - Conform to IEC 61009 - 1, IEC 62423 (F type) - Voltage independent tripping except Cat.No 4 106 57/58/59 - AC type : detect AC components faults - A type : detect AC and DC component faults - F type (High immunity) : detect faults with AC and DC components, increased immunity to false tripping - Detection of high frequency fault currents - For mounting on the right - hand side of 1 module per pole DX³ MCBs
- 2-pole - 230 V~A Type - Sensitivity : 30 mA - Nominal rating In : 40 A - Number of modules : 2

Documentation

TECHNICAL DOCUMENTATION

- G8191D.pdf | PDF (1.06Mo)
- F01305EN-05.pdf | PDF (0.39Mo)
- F01305FR_05.pdf | PDF (0.45Mo)

CAD & Design specs / BIM

- 410408.dwg | DWG (0.19Mo)

CATALOGUE PAGE & OTHERS

- ex223001_0076-0077.pdf | PDF (0.2Mo)
- ex223001_0071.pdf | PDF (0.06Mo)

Agreements & Certificates

- NF-NF012_1340 | (0.79Mo)
- LGRP-00802-V01.01-EN.pdf | PDF (0.64Mo)
- OC / CB-IT-11142 | (0.36Mo)