

Product sheet



EKINOX3 LEGRAND

Distribution board 63A MCB 8 ways

REF. 507502 | EAN. 8904129885031

> [Visit e-catalogue](#)

Product characteristics

- 8 Ways
- 24 Poles
- IP43 IK11
- Up to 250 A
- Compliant to IEC 61439-5

The product's benefits

Installation

- Product Supplied with surface or flush mounting box, door with handle, faceplate, fully isolated tin-plated copper busbar and supplied with 2 neutral bar, 2 earth bar and cable ties for cable management

Usage

- Range available, from 12 to 54 poles (from 4 to 18 ways), flush or surface mounting with same item and equipped with rail for MCBs or with mounting plate for MCCBs (maximum rating 125 A or 250 A)


Advantages

- Reversible door can be easily removed
- Shrouded neutral bars and insulated DIN rail extremities for sufficient shock absorption
- Integrated earthing system in order to avert risky contact

Documentation

TECHNICAL DOCUMENTATION

→ [LE13145AA \(1\).pdf](#) | PDF (1.28Mo)

 [New Convivio technical sheet F03444-EN-00.pdf](#) | PDF (1.25Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0308.pdf](#) | PDF (0.09Mo)

 [ex223001_0309.pdf](#) | PDF (0.05Mo)