

Product sheet



ARTEOR™ WITH NETATMO LEGRAND

Arteor™ with Netatmo - Connected switch (with dimmer option)

REF. 574230A | EAN. 3414972315845

> [Visit e-catalogue](#)

Product characteristics

- Without neutral, 5 VA - 125VA, supplied with a bleeder
- Compatible with conventional or dimmer bulbs, including LEDs. Dimmer mode can be activated from the app
- LED indicator with locator function which can be activated in the app
- Auxiliary entry for mechanical push-button control
- Champagne

Recommendation / Restriction

- To connect your switch (with dimmer option), you first need to purchase and install a Arteor with Netatmo connected starter pack. To control your two-way switch, you need to pair one or more Arteor with Netatmowireless switches with it or a mechanical push-button in english version

The product's benefits

Installation

- The Arteor with Netatmo connected switch (with dimmer option) is easily installed in place of an existing flush-mounting switch and needs a standard-depth flush-mounting box(40 mm).Compatible with claw-fixing boxes.

Usage

- Control and dim your lights by touching the switch, your smartphone or by your voice using a vocal assistant

Avantages

- When associated to the connected starter pack, the Arteor with Netatmo products can be controlled manually or remotely from your smartphone or via voice control.
- Does not require neutral. Supplied with a bleeder for increased compatibility with LED lighting on the market

Documentation

TECHNICAL DOCUMENTATION

→ [LE13978AA.pdf](#) | PDF (11.86Mo)

 [F02619EN-03.pdf](#) | PDF (1.03Mo)

Agreements & Certificates

 [OC / CB-FR_717742](#) | (0.53Mo)

 [LGRP-01679-V01.01-FR.pdf](#) | PDF (0.85Mo)

 [Decl. UE RED-A 4048 C](#) | (0.44Mo)