


# Product sheet



ARTEOR™ LEGRAND

Universal dimmer without neutral 2 wires 125W Arteor magnesium

REF. 572739A | EAN. 3414972447386

This universal light dimmer supports all "Dimmable" type bulbs on the market, LEDs, Halogens, Fluocompact, etc. It allows you to create a luminous atmosphere while reducing your energy consumption.

> [Visit e-catalogue](#)

## Description

This universal light dimmer supports all "Dimmable" type bulbs on the market, LEDs, Halogens, Fluocompact, etc. It allows you to create a luminous atmosphere while reducing your energy consumption.

### Product characteristics

- Allows you to control Dimmable bulbs of the market, LEDs, halogen, compact fluorescent
- Power : 125W max. Dimmable Leds/Fluocompact/Halogen
- Without neutral
- Compatible box depth 40mm
- MAGNESIUM

## Documentation

### TECHNICAL DOCUMENTATION

-  F03678EN-02.pdf | PDF (1.07Mo)
-  LE14408AA.pdf | PDF (6.54Mo)
-  F03678FR-02.pdf | PDF (1.08Mo)

## The product's benefits

### Installation

- Auxiliary entry for mechanical push-button control

### Usage

- Universal dimmer - Upper and lower light adjustment

### Avantages

- Universal dimmer. Compatibility with a wide range of "Dimmable" LED bulbs

### CATALOGUE PAGE & OTHERS

-  ex223001\_0564.pdf | PDF (0.06Mo)
-  ex223001\_0563.pdf | PDF (0.18Mo)