

Product sheet



LINKEO LEGRAND

PDU, Zero-U, 1 phase 16A, 20 C13 outlets + 4 C19 outlets, with cord locking

REF. 646961 | EAN. 3414972471381

[> Visit e-catalogue](#)

Product characteristics

- 1 phase - 16A
- 20 C13 outlets + 4 C19 outlets, with cord locking system
- Max power 3,7kW
- C20 inlet

The product's benefits

Installation

- Easy installation thanks to the 330° rotating cable input for a perfect orientation of the cable and no interference in the cabinet. Numbered outlets to ease the identification of each server. Supplied with 2 sets of metal fixings: button for screwless fixing, or standard screw-type brackets.

Usage

- Each C13 and C19 outlets are numbered gradually from the input and equipped with cord locking system to avoid any accidental disconnection (100 Newton retention force)

Advantages

- High ambient temperature rating: 60°C
- 330° rotative cable inlet
- Numbered outlets

Documentation

TECHNICAL DOCUMENTATION

- [LE13706AC.pdf](#) | PDF (2.71Mo)
- [User_Guide_LinkeoDC_PDUs_4.0.33.pdf](#) | PDF (8.73Mo)
- [FT-646961-EN-02.pdf](#) | PDF (1.32Mo)
- [FT-646961-FR-02.pdf](#) | PDF (1.32Mo)

CAD & Design specs / BIM

CATALOGUE PAGE & OTHERS

- [ex223001_1039.pdf](#) | PDF (0.18Mo)

Agreements & Certificates

Basic PDU.rfa | RFA (4.21Mo)
PDU basique.rfa | RFA (4.21Mo)

-  LGRP-01787-V01.01-EN.pdf | PDF (1.36Mo)
-  Decl. UE RED-NN23O9J5 001 | (0.64Mo)
-  LGRP-01787-V01.01-FR.pdf | PDF (1.31Mo)

Software & configurators

 PDU_LDC_040033-49667_ReleaseNotes.pdf | PDF (0.85Mo)