

Product sheet



LEGRAND

Programmable time switch digital disp.- for outdoor illuminations - 1 output

REF. 412654 | EAN. 3245064126540





[> Visit e-catalogue](#)

Product characteristics

- Programmable time switches - with digital display - For switching an electric circuit (lighting, heating) ON or OFF at selected times during a pre - programmed time period - Temporary (automatic return) or permanent (forced switching ON or OFF) override on output
- Multiple functions - daily or weekly programme - 5 years clock working reserve - Programme settings : on daily or weekly basis 15 languages - A programme consists of a on and off time and their assignment to certain days - Option to suspend the programme for a specific period to set - up with start and date - Minimum programme setting : 1 s. - High precision clock : $\pm 0,1$ sec per day - Particularly suited to irregular cycles : - security installations (access point, alarms, etc.) , - industrial installations (pump stations, etc.) - Programmed directly on keypad, or using program transfer key Cat.No 4 128 72 - Additional functions including random (irregular cycles) , hour counters Power supply 230 V~ - 50/60 Hz - 1 output 16 A - 250 V~ - Astronomical function - 56 programmes - $\cos \phi = 1$ per 1 inverter contact - Number of modules : 2

Documentation




TECHNICAL DOCUMENTATION

-  [Guide_Time_Switch_App_EN.pdf](#) | PDF (4.29Mo)
-  [292568GB-03.pdf](#) | PDF (1.53Mo)
-  [Guide_Time_Switch_App_FR.pdf](#) | PDF (4.23Mo)
-  [292568FR-03.pdf](#) | PDF (1.63Mo)

CAD & Design specs / BIM

-  [412654.dwg](#) | DWG (0.11Mo)

CATALOGUE PAGE & OTHERS

-  [ex223001_0100.pdf](#) | PDF (0.09Mo)
-  [ex223001_0101.pdf](#) | PDF (0.09Mo)
-  [BR TIME SWITCHES MOD CTRL AU_EN LEG4079.pdf](#) | PDF (3.49Mo)

Agreements & Certificates

-  [LGRP-00527-V01.01-EN.pdf](#) | PDF (0.63Mo)