

Product sheet



LEGRAND

Programmable time switch digital disp. -120 V~ - multifunction 56 prog. -1 output

REF. 412632 | EAN. 3245064126328

> [Visit e-catalogue](#)

Product characteristics

- Programmable time switches - with digital display - For switching an electric circuit (lighting, heating) ON or OFF at selected times during a pre - programmed time period - Temporary (automatic return) or permanent (forced switching ON or OFF) override on output
- Multiple functions - daily or weekly programme - 5 years clock working reserve - Programme settings : on daily or weekly basis 15 languages - A programme consists of a on and off time and their assignement to certain days - Option to suspend the programme for a specific period to set - up with start and date - Minimum programme setting : 1 s. - High precision clock : $\pm 0,1$ sec per day - Particularly suited to irregular cycles : - security installations (access point, alarms, etc.) , - industrial installations (pump stations, etc.) - Programmed directly on keypad, or using program transfer key Cat.No 4 128 72 - Additional functions including random (irregular cycles) , hour countersPower supply 230 V~ - 50/60 Hz - 1 output 16 A - 120 V~ - 56 programmes - $\cos \varphi = 1$ per 1 inverter contact - Number of modules : 2

Documentation

TECHNICAL DOCUMENTATION

→ [292555GB-03.pdf](#) | PDF (1.1Mo)

→ [292555FR-03.pdf](#) | PDF (1.15Mo)

CAD & Design specs / BIM

 [412721.dwg](#) | DWG (0.11Mo)

CATALOGUE PAGE & OTHERS

 [ex223001_0100.pdf](#) | PDF (0.09Mo)

 [ex223001_0101.pdf](#) | PDF (0.09Mo)

Agreements & Certificates

 [LGRP-00527-V01.01-EN.pdf](#) | PDF (0.63Mo)