

# Product sheet



LEGRAND

Wireless interconnectable smoke alarm detector - 85 dB at 3 meters

REF. 040528 | EAN. 3245060405281

> [Visit e-catalogue](#)

## Product characteristics

- Technical alarm detectors for domestic premises - smoke alarm detectors, monoxide alarm detector, Accessories
- Wireless interconnectable smoke alarm detector - Detects the smoke - Conform to EN 14604, CE CPR and NF DAAF approved (by AFNOR certification) - Photoelectric technology guarantee without radioelement - Gives a loud signal : 85 dB at 3 meters - Powered by lithium battery (lifetime : 10 years, not replaceable) - Life cycle of 10 years : Due date indicated on the product - Can be interconnected with 10 devices : - Cat.No 0 405 28 (smoke alarm detector) or Cat.No 0 405 14 (relay) - When one device detects, all interconnected devices go into alarm - Can be interconnected with My Home intruder alarm - Suitable for housing with more one floor or more one device - Fitted with : - Push function : in case of false alarm permit to stop the alarm sound for 10 minutes - grid insect protection (to avoid false alarm) - Anti-theft function (suitable for rental housing a tool is necessary to take off the detector) - Delivered with screws and battery - Made in France

## Documentation

### TECHNICAL DOCUMENTATION

→ [LE06149AC.pdf](#) | PDF (23.36Mo)

### CATALOGUE PAGE & OTHERS

 [ex223001\\_0871.pdf](#) | PDF (0.04Mo)