

Product sheet



LCS³ LEGRAND

LCS³ 19" PDU 1U 6 x 2P+E german standard with 3m power supply cord equipped with a MCB 1P C16 6kA

REF. 646831 | EAN. 3414970765529

PDU 19 inches 1U with 6 x 2P+E german standard outlets, to supply power to equipment in 19 inches enclosures. With aluminium casing, socket modules, a mounting and a termination solution. With additional MCB C16 6kA.

> [Visit e-catalogue](#)

Description

PDU 19 inches 1U with 6 x 2P+E german standard outlets, to supply power to equipment in 19 inches enclosures. With aluminium casing, socket modules, a mounting and a termination solution. With additional MCB C16 6kA.

Product characteristics

- Single phase
- 6 x 2P+E german standard outlets equipped with protective shutters
- Input voltage 230V
- Input current 16A
- Maximum power 3,7kW

The product's benefits

Installation

- Quick fixing (no screws) on 19 inches fixing centers. Can also be installed vertically by reverting the brackets (no screws).

Usage


- Equipped with a MCB (Mini Circuit Breaker) 16A 1P 6kA for protecting equipment against short-circuits and overloads

Avantages

- Angle of outlets is 55°

Documentation

TECHNICAL DOCUMENTATION

 S000093176EN-15.pdf | PDF (3.09Mo)

 S000093176FR-15.pdf | PDF (3.1Mo)

Agreements & Certificates

 LGRP-01740-V01.01-EN.pdf | PDF (0.91Mo)

CATALOGUE PAGE & OTHERS

 ex223001_1016.pdf | PDF (0.19Mo)