

# Product sheet



## VALENA LIFE LEGRAND

2-way switch with neutral Valena In'Matic - 10 AX 250 V~

REF. 752010 | EAN. 3414970465290

> [Visit e-catalogue](#)

## Product characteristics

- Valena™ IN'MATIC mechanisms - switches - Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting - Supplied with mounted dust protection transparent shield - To be equipped with Valena Life or Valena Allure cover plates and plates - Packaged in boxes
- Switches 10 AX - 250 V~Two-way switch with neutral terminal - Automatic terminals - Becomes illuminated with LED Cat.No 0 676 86 or 7 520 57 (surround lighting in Valena Allure range) - Indicator version: with LED Cat.No 0 676 88 or 7 520 58 (surround lighting in Valena Allure range) - Possibility to wire a lamp (locator or indicator version) between the phase and the neutral terminals, to avoid the "ghost effect"

## Documentation

### TECHNICAL DOCUMENTATION

 F02081FR-01.pdf | PDF (0.63Mo)

 F02081EN-01.pdf | PDF (0.63Mo)

→ LE09162AH.pdf | PDF (4.47Mo)

### Agreements & Certificates

 OC / CB-FR\_711212 | (1.01Mo)

### CAD & Design specs / BIM

 752001\_AIICATPart.stp | IFC (20.43Mo)