

CAT. N° 0 014 41



FLUSH-MOUNTING CABINET NEDBOX - METAL DOOR WHITE RAL 9010 - 1 ROW - 12+2 MODULES

Pack (number of units)	1
Volume (dm ³)	17,672
Weight (g)	2 568,00

Product characteristics

Flush-mounting distribution cabinets

- White RAL 9003
- Supplied with:
 - reversible door
 - screw terminal blocks for neutral and earth
- Spacing between rails 125 mm
- For installation in dry partitions use the flush-mounting kit Cat.No 0 014 90
- Number of rows : 1
- Number of modules : 12 + 2
- Height : 305 mm
- Width : 330 mm
- Depth : 87 mm

General characteristics

Flush-mounting cabinets Nedbox - 12 to 48 modules

- IP 40 - IK 07
- Class II
- Allows to achieve assemblies conform to IEC 61439-3
- Self extinguishing: resistance to incandescent wire 850° C

Documentation

Catalogue pages & additional information

- [Description page \(p.215\)](#)

Installation & technical data

- [F02428EN](#)

Environmental product profile

- [Environnemental product sheet n°A E4051B-EN](#)

Installation instructions & related documents

- [LE04724AA](#)

Agreements & certificates of conformity

- [LOVAG - IT 16.040](#)