

CAT. N° 0 014 42



## FLUSH-MOUNTING CABINET NEDBOX - METAL DOOR WHITE RAL 9010 - 2 ROWS - 24+4 MODULES

Pack (number of units)	1
Volume (dm <sup>3</sup> )	23,936
Weight (g)	3 375,00

### Product characteristics

#### Flush-mounting distribution cabinets

- White RAL 9003
- Supplied with:
  - reversible door
  - screw terminal blocks for neutral and earth
- Spacing between rails 125 mm
- For installation in dry partitions use the flush-mounting kit Cat.No 0 014 90
- Number of rows : 2
- Number of modules : 24 + 4
- Height : 430 mm
- Width : 330 mm
- Depth : 87 mm

### General characteristics

#### Flush-mounting cabinets Nedbox - 12 to 48 modules

- IP 40 - IK 07
- Class II
- Allows to achieve assemblies conform to IEC 61439-3
- Self extinguishing: resistance to incandescent wire 850° C

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.215\)](#)



#### Installation & technical data

- [F02428EN](#)



#### Environmental product profile

- [Environnemental product sheet n°A E4051B-EN](#)



#### Installation instructions & related documents

- [LE04724AA](#)



#### Agreements & certificates of conformity

- [LOVAG - IT 16.040](#)