

CAT. N° 0 014 51

**FLUSH-MOUNTING CABINET NEDBOX - TRANSPARENT DOOR - 1 ROW - 12+2 MODULES**

Pack (number of units)	1
Volume (dm <sup>3</sup> )	17,672
Weight (g)	2 436,00

**Product characteristics****Flush-mounting distribution cabinets**

- White RAL 9003
- Supplied with:
  - reversible door
  - screw terminal blocks for neutral and earth
- Spacing between rails 125 mm
- For installation in dry partitions use the flush-mounting kit Cat.No 0 014 90

**With transparent door**

- Number of rows : 1
- Number of modules : 12 + 2
- Height : 305 mm
- Width : 330 mm
- Depth : 87 mm

**General characteristics****Flush-mounting cabinets Nedbox - 12 to 48 modules**


- IP 40 - IK 07
- Class II
- Allows to achieve assemblies conform to IEC 61439-3
- Self extinguishing: resistance to incandescent wire 850° C

**Documentation** **Catalogue pages & additional information**

- [Description page \(p.215\)](#)

 **Installation & technical data**

- [F02428EN](#)

 **Environmental product profile**

- [Environnemental product sheet n°A E4051B-EN](#)

 **Installation instructions & related documents**

- [LE04724AA](#)

 **Agreements & certificates of conformity**

- [LOVAG - IT 16.040](#)