

REF . 0 019 17



## MULTIFUNCTION SLEEVE - VERTICAL - FOR 2 ROWS CABINETS



Emballage (nombre number of units )	1
Volume (dm <sup>3</sup> )	8,975
Poids (g)	1 237,00

### Caractéristiques du produit

#### Multifunction sleeves

- Supplied with hinges connecting the cover to the back of the cabinet
- For use with 12 and 18-module cabinets using joining kit Cat.No 0 019 67
- Can be fitted with control units and accessories: P17 16 A and 32 A sockets with standard fixing centres, flush-mounted IP 55 Plexo wiring accessories, Osmoz, modular rail at the back of the box

#### Vertical

- For 2 rows cabinets

### Caractéristiques générales

#### Plexo<sup>3</sup> - IP 65 weatherproof cabinets, multifunction sleeves and accessories

- Self-extinguishing: resistance to incandescent wire 650°C.
- Allows to achieve assemblies conform to IEC 61 439 - 3
- Weatherproof cabinets - IP 65 - IK 09 - Class II
- Door and cabinet fully reversible. Removable chassis and faceplates from 2-row versions up
- 2-position rail for modular products and moulded cases. Spacing between rails 150 mm
- Can be fitted with perforated plates and solid faceplates for mounting non-modular products
- Lockable door handle, sealable cover and faceplate
- Shock-resistant polystyrene material
- Box colour light grey L750A, cover colour dark grey R746A
- Supplied without terminal blocks

### Documentation associée



#### Catalogue pages & additional information

- [Description page \(p.286\)](#)
- [Technical page \(p.287\)](#)



#### Agreements & certificates of conformity

- [OC / CB-654748](#)



#### Installation & technical data

- [EXB14046\\_CA\\_Plexo3\\_EN\\_print](#)