

CAT. N° 0 019 62



PERFORATED FACEPLATE - FOR PLEXO³ CABINETS - FOR 12 MODULES CABINETS - H. 150 MM

Pack (number of units)	2
Volume (dm ³)	0,344
Weight (g)	393,00

Product characteristics

Accessories

Perforated plates

- Allow the DIN rail to be replaced with a Lina 25 plate when integrating non-modular products
- For 12 modules cabinets, Height 150 mm

General characteristics

Plexo³ - IP 65 weatherproof cabinets, multifunction sleeves and accessories

- Self-extinguishing: resistance to incandescent wire 650°C.
- Allows to achieve assemblies conform to IEC 61 439 - 3
- Weatherproof cabinets - IP 65 - IK 09 - Class II
- Door and cabinet fully reversible. Removable chassis and faceplates from 2-row versions up
- 2-position rail for modular products and moulded cases. Spacing between rails 150 mm
- Can be fitted with perforated plates and solid faceplates for mounting non-modular products
- Lockable door handle, sealable cover and faceplate
- Shock-resistant polystyrene material
- Box colour light grey L750A, cover colour dark grey R746A
- Supplied without terminal blocks

Documentation

Catalogue pages & additional information

- [Description page \(p.286\)](#)
- [Technical page \(p.287\)](#)

Agreements & certificates of conformity

- [OC / CB-654748](#)

Installation instructions & related documents

- [LE02499AB](#)