

CAT. N° 0 037 10



PROGRAMMABLE TIME SWITCH WITH DIGITAL DISPLAY - WEEKLY 230 V~ - 50/60 HZ - 1 NO CONTACT - 1 MODULE

Pack (number of units)	10
Volume (dm ³)	2,238
Weight (g)	934,00

Product characteristics

Weekly time switch

- Time-saving programming by selection of daily blocks, daily blocks individually adjustable or selection from preset blocks Mo-Fr and Mo-Su
- Permanent ON or OFF
- Circuit anticipation
- Power reserve 3 years for date, time and switching program
- Accuracy +/- 1 sec./Day

Power supply 230 V~ - 50/60 Hz

- 1 NO contact
- 250 V/50 Hz 16 A - cos Ø = 1
- 28 programmes
- Shortest switching-time 1 min
- Number of modules : 1

General characteristics

Programmable time switches - with digital display

- For switching an electric circuit (lighting, heating) ON or OFF at selected times during a pre-programmed time period
- Temporary (automatic return) or permanent (forced switching ON or OFF) override on output

Documentation

Catalogue pages & additional information

- [Description page \(p.090\)](#)
- [Technical page \(p.091\)](#)
- [Dimensions of din-rail equipment](#)

Agreements & certificates of conformity

- [VDE-40044959](#)

Installation instructions & related documents

- [290922-02](#)