

CAT. N° 0 048 68

**DISTRIBUTION TERMINAL - 250 A - 6 OUPUTS FLEXIBLE :
4 X 35 MM² 2 X 25 MM²**


Pack (number of units)	1
Volume (dm ³)	0,22
Weight (g)	163,00

Product characteristics**Distribution terminals**

- 250 A - 4 outputs 35 mm² flexible and 2 outputs
- 25 mm² flexible - I_{sc} peak 36 kA
- Can be fitted directly onto downstream terminal of DPX-IS 250

General characteristics**Modular distribution blocks 40 to 250 A**

- Standard distribution
- Connection with or without Starfix ferrules
- Self-extinguishing, according to EN 60695-2-11: 960 °C on active part supports

Documentation **Catalogue pages & additional information**

- [Selection chart \(p.198\)](#)
- [Description page \(p.201\)](#)
- [Modular distribution blocks](#)