

CAT. N° 0 048 88



## MONOBLOC MODULAR DISTRIBUTION BLOCK - 4P - 125 A - 15 CONNECTIONS

Pack (number of units)	5
Volume (dm <sup>3</sup> )	4,459
Weight (g)	2 181,00

### Product characteristics

#### Monobloc modular distribution blocks

- Mounting on rail or on plate with 2 screws
- Supplied with insulated back plate and transparent protective front cover
- Each bar can be labelled using CAB 3
- Possible to add IP 2X terminal block

#### Four pole

- Equipped with 4 bars
- With short ferrule supplied for flexible connection 25 mm<sup>2</sup>
- Rating : 125 A
- Isc peak : 14.5 kA
- Icw : 4.2 kA
- Number of modules : 8

### General characteristics

#### Modular distribution blocks 40 to 250 A

- Standard distribution
- Connection with or without Starfix ferrules
- Self-extinguishing, according to EN 60695-2-11: 960 °C on active part supports

### Documentation



#### Catalogue pages & additional information

- [Selection chart \(p.198\)](#)
- [Description page \(p.201\)](#)
- [Modular distribution blocks](#)