

CAT. N° 0 058 12



## FUSE CARRIER - FOR DOMESTIC CYLIND CARTRIDGE FUSE 8.5 X 31.5 MM - 20 A - 1P

Pack (number of units)	10
Volume (dm <sup>3</sup> )	1,619
Weight (g)	784,00

### Product characteristics

#### For domestic cylindrical cartridge fuses

- Conform to EN 60269-1 and IEC 60269-1,3

#### Single pole

- For domestic cartridges : 20 A - 400 V~
- Cartridge dimensions : 8.5 x 31.5 mm
- Number of modules : 1

### General characteristics

#### Domestic fuse carriers

- With label-holders
- With insulated carrier class II, padlockable
- Coupling via supply busbars
- Shielded terminals capacity 2 x 10 mm<sup>2</sup>
- Possibility to signal indicator blown fuse
- Fuse not supplied

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.082\)](#)
- [Dimensions of din-rail equipment](#)

#### Agreements & certificates of conformity

- [NF - 655175](#)

#### Installation & technical data

- [fa221ben](#)