

CAT. N° 0 104 63



FLEXIBLE COVER UNIVERSAL DLP TRUNKING WITHOUT PARTITION 35 X 105 MM - 85 MM COVER - 2 M

Pack (number of units)	20
Volume (dm ³)	83,597
Weight (g)	19 400,00

Product characteristics

Flexible cover universal trunking 35 x 105

Trunking without partition

- Supplied with:
 - one 35 x 105 mm body
 - one flexible 85 mm width cover
- Fits onto the whole trunking including in internal and external angles
- Installation: can be used with Mosaic/Arteor ranges or DIN rail equipment
- Length 2 m

General characteristics

Flexible cover universal DLP trunking 35 x 105 and 50 x 105 - 85 mm cover

- White

Documentation

Catalogue pages & additional information

- [Selection chart \(p.820\)](#)
- [Description page \(p.824\)](#)
- [Flexible cover universal DLP trunking](#)

Agreements & certificates of conformity

- [NF 004-601796A](#)

Installation & technical data

- [F00885EN-03](#)

Environmental product profile

- [LGRP-00950-V01-01-EN](#)