

CAT. N° 0 104 67



FLEXIBLE COVER DLP TRUNKING - 50 X 170 - 3 COVERS 40/65/40 MM - 2 M - WHITE

Pack (number of units)	4
Volume (dm ³)	40
Weight (g)	8 100,00

Product characteristics

Flexible cover universal trunking 50 x 170

Trunking with partition

- Supplied with:
 - one 50 x 170 mm body
 - one flexible 65 mm width cover and two flexible 40 mm width covers
- Fits onto the whole trunking including internal and external angles
- Installation: can be used with Mosaic/Arteor ranges or DIN rail equipment
- Length 2 m

General characteristics

Flexible cover universal DLP trunking 50 x 150 and 50 x 170 - 65 mm cover

- White

Documentation

Catalogue pages & additional information

- [Selection chart \(p.820\)](#)
- [Description page \(p.823\)](#)
- [Flexible cover universal DLP trunking](#)

Agreements & certificates of conformity

- [NF 004-601796A](#)

Installation & technical data

- [F00885EN-03](#)

Environmental product profile

- [LGRP-00950-V01-01-EN](#)