

CAT. N° 0 104 70



FLEXIBLE COVER UNIVERSAL DLP TRUNKING WITH PARTITION 50 X 195 MM - 2 X 85 MM COVER - 2 M

Pack (number of units)	8
Volume (dm ³)	74,603
Weight (g)	17 000,00

Product characteristics

Flexible cover universal trunking 50 x 195

Trunking with partition

- Supplied with:
 - one 50 x 195 mm body
 - two flexible 85 mm width covers
- Fits onto the whole trunking including in internal and external angles
- Installation: can be used with Mosaic/Arteor ranges or DIN rail equipment
- Length 2 m

General characteristics

Flexible cover universal DLP trunking 50 x 195 - 85 mm cover

- White

Documentation

Catalogue pages & additional information

- [Selection chart \(p.820\)](#)
- [Description page \(p.825\)](#)
- [Flexible cover universal DLP trunking](#)

Agreements & certificates of conformity

- [NF 004 - 601796A](#)

Installation & technical data

- [F00885EN-03](#)
- [F00885FR-03](#)