

CAT. N° 0 105 80



HEIGHT SPACER LENGTH 2 M - FOR FLEXIBLE COVER SNAP-ON DLP TRUNKING - CHARCOAL GREY

Pack (number of units)	24
Volume (dm ³)	14,123
Weight (g)	3 400,00

Product characteristics

Flexible cover snap-on trunking

Height spacer

- Length 2 m, colour charcoal grey
- For fitting 15 mm from the ground

General characteristics

Flexible cover snap-on DLP trunking 45 mm cover 50 x 180 - routing sections and accessories

Documentation

Catalogue pages & additional information

- [Description page \(p.813\)](#)
- [Description page \(p.814\)](#)
- [Description page \(p.815\)](#)
- [Flexible cover snap-on DLP trunking](#)

Installation & technical data

- [F00886EN-05](#)
- [F00886FR-04](#)

Environmental product profile

- [LGRP-00951-V01](#)

Installation instructions & related documents

- [104870090-03](#)

Agreements & certificates of conformity

- [NF 004-601796A](#)