

REF . 0 106 21


**EXTERNAL BEND 60-120° - FOR FLEXIBLE COVER DLP TRUNKING HEIGHT 35 - WHITE**


Emballage (nombre number of units )	10
Volume (dm <sup>3</sup> )	5,638
Poids (g)	396,00

**Caractéristiques du produit**
**Angles for flexible cover universal trunking 35 x 105**
**Internal and external bends**

- Include the 2 components for the top and bottom of the trunking on which the flexible cover is fitted
- Changeable external bend, from 60° to 120° for 35 x 80 and 35 x 105 mm trunking

**Caractéristiques générales**
**Flexible cover universal DLP trunking 35 x 105 and 50 x 105 - 85 mm cover**

- White

**Documentation associée**

**Catalogue pages & additional information**

- [Selection chart \(p.820\)](#)
- [Description page \(p.824\)](#)
- [Flexible cover universal DLP trunking](#)


**Agreements & certificates of conformity**

- [NF 004-601796A](#)


**Installation & technical data**

- [F00885EN-03](#)


**Environmental product profile**

- [LGRP-00950-V01-01-EN](#)