

CAT. N° 0 106 50



## INTERNAL BEND 85-95° - FOR FLEXIBLE COVER DLP TRUNKING 50X170

Pack (number of units)	5
Volume (dm <sup>3</sup> )	9,106
Weight (g)	574,00

### Product characteristics

#### Angles for flexible cover universal trunking 50 x 170

##### Internal and external bends

- Include the 4 components making the angle (parts for the top and bottom and the 2 partition junctions) on which the flexible cover is fitted
- Changeable internal bend, from 85° to 95° for 50 x 170 and 50 x 195 mm trunkings

### General characteristics

#### Flexible cover universal DLP trunking 50 x 150 and 50 x 170 - 65 mm cover

- White

### Documentation

#### Catalogue pages & additional information

- [Selection chart \(p.820\)](#)
- [Selection chart \(p.821\)](#)
- [Description page \(p.823\)](#)
- [Flexible cover universal DLP trunking](#)

#### Agreements & certificates of conformity

- [NF 004-601796A](#)

#### Installation & technical data

- [F00885EN-03](#)

#### Environmental product profile

- [LGRP-00950-V01-01-EN](#)