

CAT. N° 0 124 02



DOMESTIC CARTRIDGE FUSE - CYLINDRICAL TYPE GG 8 X 32 - 2 A - WITH INDICATOR

Pack (number of units)	10
Volume (dm ³)	0,035
Weight (g)	42,00

Product characteristics

Cylindrical type gG

- Conform to EN 60269-1, IEC 60269-1 and 2

8 x 32 (previously 8.5 x 31.5)

- With indicator
- Rating : 2 Amps
- Voltage ~ : 400 Volts
- Rupture capacity : 20000 Amps

General characteristics

HRC cartridge fuses

Documentation



Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)



Installation & technical data

- [F00192EN-09](#)