

CAT. N° 0 124 06

**DOMESTIC CARTRIDGE FUSE - CYLINDRICAL TYPE GG 8 X 32 - 6 A - WITH INDICATOR**

Pack (number of units)	10
Volume (dm ³)	0,036
Weight (g)	43,00

Product characteristics**Cylindrical type gG**

- Conform to EN 60269-1, IEC 60269-1 and 2

8 x 32 (previously 8.5 x 31.5)

- With indicator
- Rating : 6 Amps
- Voltage ~ : 400 Volts
- Rupture capacity : 20000 Amps

General characteristics**HRC cartridge fuses****Documentation****Catalogue pages & additional information**

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)

**Installation & technical data**

- [F00192EN-08](#)