

CAT. N° 0 124 10



## DOMESTIC CARTRIDGE FUSE - CYLINDRICAL TYPE GG 8 X 32 - 10 A - WITH INDICATOR

Pack (number of units)	10
Volume (dm <sup>3</sup> )	0,035
Weight (g)	44,00

### Product characteristics

#### Cylindrical type gG

- Conform to EN 60269-1, IEC 60269-1 and 2

#### 8 x 32 (previously 8.5 x 31.5)

- With indicator
- Rating : 10 Amps
- Voltage ~ : 400 Volts
- Rupture capacity : 20000 Amps

### General characteristics

#### HRC cartridge fuses

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)



#### Installation & technical data

- [F00192EN-09](#)