

CAT. N° 0 133 16



HRC CARTRIDGE FUSE - CYLINDRICAL TYPE GG 10 X 38 - 16 A - WITHOUT INDICATOR

Pack (number of units)	10
Volume (dm ³)	0,056
Weight (g)	78,00

Product characteristics

Cylindrical type gG

- Conform to EN 60269-1, IEC 60269-1 and 2

10 x 38 HRC

- Without indicator
- Rating : 16 Amps
- Voltage ~ : 500 Volts
- Rupture capacity : 100000 Amps

General characteristics

HRC cartridge fuses

Documentation

Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)

Agreements & certificates of conformity

- [LRS \(Lloyd's\) - 13/00020\(E1\)](#)

Installation & technical data

- [F00192EN-08](#)