

CAT. N° 0 146 53



CAM SWITCH - VOLTMETER - PR 12 - 16 A - 6 CONTACTS -3 CT WITH NEUTRAL - SCREW FIXING

Pack (number of units)	1
Volume (dm ³)	0,521
Weight (g)	145,00

Product characteristics

Function: selective measurement switches

Voltmeters

- Range : PR 12
- Max. rating AC 21 : 16 A
- Number of contacts : 6
- Function : with neutral

General characteristics

Cam switches screw fixing on door

- For selecting and changing the status of the circuits into which it is integrated
- For viewing the state of equipment according to the position of the selector lever
- Mounting on enclosure doors
- Contacts with positive opening and double breaking of poles
- Presentation: grey/black selector lever - aluminium faceplate with marking
- Conform to standards IEC EN 60947-3
- Approved to UL-CSA (USA - Canada)
- IP 40 at front of enclosure (selector lever)
- IP 2X at back of enclosure up to PR 26

Documentation



Catalogue pages & additional information

- [Description page \(p.358-359\)](#)



Installation instructions & related documents

- [096876000-00](#)
- [096897001-01](#)