

CAT. N° 0 150 96



## HRC CARTRIDGE FUSE - CYLINDRICAL TYPE AM 22 X 58 - 100 A - WITHOUT INDICATOR

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 10     |
| Volume (dm <sup>3</sup> ) | 0,381  |
| Weight (g)                | 526,00 |

### Product characteristics

#### Cylindrical type aM (motor rated)

- Conform to EN 60269-1, IEC 60269-1 and 2

#### 22 x 58 HRC

- Without striker
- Rating : 100 Amps
- Voltage ~ : 500 Volts
- Rupture capacity : 100000 Amps

### General characteristics

#### HRC cartridge fuses

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)



#### Installation & technical data

- [F00188EN-06](#)