

CAT. N° 0 150 97



HRC CARTRIDGE FUSE - CYLINDRICAL TYPE AM 22 X 58 - 125 A - WITHOUT INDICATOR

Pack (number of units)	10
Volume (dm ³)	0,381
Weight (g)	530,00

Product characteristics

Cylindrical type aM (motor rated)

- Conform to EN 60269-1, IEC 60269-1 and 2

22 x 58 HRC

- Overrating not described by standards
- Without striker
- Rating : 125 Amps
- Voltage ~ : 400 Volts
- Rupture capacity : 100000 Amps

General characteristics

HRC cartridge fuses

Documentation



Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)



Installation & technical data

- [F00188EN-06](#)