

CAT. N° 0 155 97



## HRC CARTRIDGE FUSE - CYLINDRICAL TYPE GG 22 X 58 - 125 A - WITH INDICATOR

Pack (number of units)	10
Volume (dm <sup>3</sup> )	0,381
Weight (g)	530,00

### Product characteristics

#### Cylindrical type gG

- Conform to EN 60269-1, IEC 60269-1 and 2

#### 22 x 58 HRC

- Overrating not described by standards
- With striker
- Rating : 125 Amps
- Voltage ~ : 400 Volts
- Rupture capacity : 100000 Amps

### General characteristics

#### HRC cartridge fuses

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.179\)](#)
- [Blade cartridge fuses gG and aM types](#)



#### Installation & technical data

- [F00192EN-09](#)