


CAT. N° 0 160 45

**HRC BLADE TYPE CARTRIDGE FUSE - CYLINDRICAL
TYPE AM 22 X 58 - 40 A - W INDICATOR**

| | |
|---------------------------|--------|
| Pack (number of units) | 3 |
| Volume (dm ³) | 0,693 |
| Weight (g) | 602,00 |

Product characteristics**Type aM (motor rated)**

- Conform to EN 60269-1, IEC 60269-1, 2 and VDE 0636-1
- Fully insulated end plate and handle lugs

Size 00

- With indicator
- Rating : 100 Amps
- Voltage ~ : 500 Volts
- Breaking capacity : 120000 Amps

General characteristics**HRC blade type cartridge fuses - gG/gL and aM types****Documentation****Catalogue pages & additional information**

- [Description page \(p.180\)](#)
- [Blade cartridge fuses gG and aM types](#)