

CAT. N° 0 163 45



## HRC BLADE TYPE CARTRIDGE FUSE - TYPE GG - SIZE 00 - 100 A - WITH INDICATOR

Pack (number of units)	10
Volume (dm <sup>3</sup> )	2,066
Weight (g)	1 983,00

### Product characteristics

#### Type gG / gL

- Conform to IEC 60269-2
- For protection against accidental contacts, use terminal shields and fuse covers supplied with protection kits

#### Size 00

- With indicator
- Rating : 100 Amps
- Voltage ~ : 500 Volts
- Breaking capacity : 120000 Amps

### General characteristics

#### HRC blade type cartridge fuses - gG/gL and aM types

### Documentation



#### Catalogue pages & additional information

- [Description page \(p.180\)](#)
- [Blade cartridge fuses gG and aM types](#)



#### Installation & technical data

- [F00189EN05](#)