

CAT. N° 0 166 45



HRC BLADE TYPE CARTRIDGE FUSE - TYPE AM - SIZE 0 - 100 A - WITH STRIKER

Pack (number of units)	3
Volume (dm ³)	2,351
Weight (g)	945,00

Product characteristics

Type aM (motor rated)

- Conform to EN 60269-1, IEC 60269-1, 2 and VDE 0636-1
- Fully insulated end plate and handle lugs

Size 0

- With striker
- Rating : 100 Amps
- Voltage ~ : 500 Volts
- Breaking capacity : 120000 Amps

General characteristics

HRC blade type cartridge fuses - gG/gL and aM types

Documentation



Catalogue pages & additional information

- [Description page \(p.180\)](#)
- [Blade cartridge fuses gG and aM types](#)



Installation & technical data

- [F00190EN-06](#)