

CAT. N° 0 168 40



HRC BLADE TYPE CARTRIDGE FUSE - TYPE GG - SIZE 0 - 80 A - WITH INDICATOR

Pack (number of units)	3
Volume (dm ³)	1,774
Weight (g)	821,00

Product characteristics

Type gG / gL

- Conform to IEC 60269-2
- For protection against accidental contacts, use terminal shields and fuse covers supplied with protection kits

Size 0

- With indicator
- Rating : 80 Amps
- Voltage ~ : 500 Volts
- Breaking capacity : 120000 Amps

General characteristics

HRC blade type cartridge fuses - gG/gL and aM types

Documentation



Catalogue pages & additional information

- [Description page \(p.180\)](#)
- [Blade cartridge fuses gG and aM types](#)



Installation & technical data

- [F00189EN05](#)