

CAT. N° 0 205 06


ROOF BASE FOR ENCLOSURE XL³ 4000 - DEPTH 975 MM - WIDTH 725 MM


| | |
|---------------------------|-----------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 216 |
| Weight (g) | 42 000,00 |

Product characteristics
Enclosures and cable sleeves modular metal
Roof-base for enclosure

- Fitted with cable entry plates
- Take the structural uprights
- Depth : 975 mm
- Width external : 725 mm
- Width usable : 600 mm

General characteristics
Distribution enclosures XL³ 4000

- IP 30 - IK 07
- IP 55 - IK 08 with door and sealing kit for use when joining enclosures
- Consist of the combination of a "roof-base" assembly, structural uprights, functional uprights, rear and side panels RAL 7035, plinths RAL 7004
- Height 2000 or 2200 mm.
- Capacity 24 modules (enclosures width 725 or width 975 with internal cable sleeve), 36 modules (enclosures width 975)
- Usable faceplate height 1800 mm (1700 mm only if using the pivoting support frame) or 2000 mm

Documentation
 **Catalogue pages & additional information**

- [Description page \(p.266\)](#)
- [Technical page \(p.267\)](#)
- [Selection chart \(p.268\)](#)
- [XL3 4000 equipment for mounting on adjustable plates](#)

 **Installation & technical data**

- [F00254EN-03](#)
- [EXB15002_CA_XL3-4000-6300_EN](#)

 **Installation instructions & related documents**

- [F0998K](#)

 **Agreements & certificates of conformity**

- [LOVAG-IT 12](#)
- [LOVAG-IT 12](#)
- [LOVAG-IT 12](#)