

CAT. N° 0 205 43



## REAR AND SIDE PANELS XL<sup>3</sup> 4000 - HEIGHT 2000 MM - WIDTH 975 MM

Pack (number of units)	1
Volume (dm <sup>3</sup> )	68
Weight (g)	22 141,00

### Product characteristics

#### Enclosures and cable sleeves modular metal

##### Rear and side panels

- Fixed with screws
- Width 975 mm
- Height : 2000 mm

### General characteristics

#### Distribution enclosures XL<sup>3</sup> 4000

- IP 30 - IK 07
- IP 55 - IK 08 with door and sealing kit for use when joining enclosures
- Consist of the combination of a "roof-base" assembly, structural uprights, functional uprights, rear and side panels RAL 7035, plinths RAL 7004
- Height 2000 or 2200 mm.
- Capacity 24 modules (enclosures width 725 or width 975 with internal cable sleeve), 36 modules (enclosures width 975)
- Usable faceplate height 1800 mm (1700 mm only if using the pivoting support frame) or 2000 mm

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.266\)](#)
- [Technical page \(p.267\)](#)
- [Selection chart \(p.268\)](#)
- [XL3 4000 equipment for mounting on adjustable plates](#)

#### Agreements & certificates of conformity

- [LOVAG-IT 12](#)
- [LOVAG-IT 12](#)
- [LOVAG-IT 12](#)

#### Installation & technical data

- [EXB15002\\_CA\\_XL3-4000-6300\\_EN](#)