

CAT. N° 0 208 05



## METAL FACEPLATE XL<sup>3</sup> 800/4000 - DPX<sup>3</sup> WITH DIRECT ROTARY HANDLE- 1/4 TURN - 24 MODULES

Pack (number of units)	1
Volume (dm <sup>3</sup> )	8,699
Weight (g)	2 307,00

### Product characteristics

#### Metal faceplates for devices in vertical position

##### For 1 to 3 DPX<sup>3</sup> with direct rotary handle

- 24 modules
- For fastening and sealing
- 1/4 turn

### General characteristics

#### Equipment for XL<sup>3</sup> 4000 - for mounting on adjustable plate: DPX<sup>3</sup> 160, DPX<sup>3</sup> 250 fixed version

### Documentation



#### Catalogue pages & additional information

- [Selection chart \(p.262-263\)](#)
- [Description page \(p.270\)](#)
- [Description page \(p.271\)](#)
- [XL3 4000 equipment for mounting on adjustable plates](#)



#### Agreements & certificates of conformity

- [LOVAG-IT 12](#)
- [LOVAG-IT 12](#)
- [LOVAG-IT 12](#)
- [LOVAG-IT 12](#)
- [LOVAG-IT 12](#)
- [LOVAG-IT 12](#)



#### Installation & technical data

- [EXB15002\\_CA\\_XL3-4000-6300\\_EN](#)