

CAT. N° 0 221 82



## PROXIMITY SWITCHING ISOLATING SWITCH - 4P NEUTRAL ON LEFT - 20 A

Pack (number of units)	1
Volume (dm <sup>3</sup> )	1,774
Weight (g)	461,00

### Product characteristics

#### Proximity switching

- Can be equipped with auxiliary contact Cat.No 0 227 00
- Padlockable boxes for on-load breaking, isolation and locking in O position
- Equipment located remotely from a control cabinet
- Applications: breaking of CMV (controlled mechanical ventilation), motors, fixed or moving machines, air-conditioners

#### 4P - neutral on left-hand side - yellow box

- 20 A

### General characteristics

#### Proximity switching from 16 to 80 A

- Safety switch for disconnection and isolation of phases
- IP 2X
- Double breaking on each phase
- Red rotary handle on yellow plate
- Immediate display of position
  - horizontal: open (O)
  - vertical: closed (I)
- Equipped with non reversible terminals
- Conform to IEC EN 60947-3
- UL-cUL (USA and Canada) agreements (except boxes)
- IP 65 - IK 07 for boxes

### Documentation

#### Catalogue pages & additional information

- [Description page \(p.176\)](#)
- [Isolator switches](#)

#### Agreements & certificates of conformity

- UL listed cULus - NLRV-E57817
- UL listed cUL - NLRV7-E57817

#### Installation instructions & related documents

- [096891000-01](#)