

CAT. N° 0 226 17



FULL LOAD SWITCH UNIT WITH VISTOP - 63 A - 4P

| | |
|---------------------------|----------|
| Pack (number of units) | 1 |
| Volume (dm ³) | 12,925 |
| Weight (g) | 1 734,00 |

Product characteristics

Full load switch units 32 to 160 A

- Comprising:
 - IP 65 plastic box with transparent hinged cover equipped with a Vistop with side red handle, yellow front plate with N/C + N/O auxiliary contact
 - earth terminal (Viking 3)

63 A - IK 07

- Supplied with 2 cable glands 29P - ISO 32
- 4P
- Connection : 50 mm² flexible - 70 mm² rigid
- Earth terminal nominal capacity : 50 mm²

General characteristics

Proximity switching 32 to 160 A

- For on-load circuit breaking, isolation and locking in 0 position equipment located remotely
- Applications:
 - breaking of CMV (controlled mechanical ventilation motors, fixed or moving machines, air-conditioners)
- Can also be used as a:
 - general switch
 - emergency stop
- IP 65

Documentation



Catalogue pages & additional information

- [Description page \(p.177\)](#)



Installation instructions & related documents

- 0064C67-05
- 0064DP106_07