

CAT. N° 0 226 33


FULL LOAD SWITCH UNIT WITH VISTOP - 125 A - 3P

Pack (number of units)	1
Volume (dm ³)	26,46
Weight (g)	3 407,00

Product characteristics
Full load switch units 32 to 160 A

- Comprising:
 - IP 65 plastic box with transparent hinged cover equipped with a Vistop with side red handle, yellow front plate with N/C + N/O auxiliary contact
 - earth terminal (Viking 3)

125 A - IK 07

- Supplied with 2 cable glands 36P - ISO 50
- 3P
- Connection : cage terminals
- Earth terminal nominal capacity : 50 mm²

General characteristics
Proximity switching 32 to 160 A

- For on-load circuit breaking, isolation and locking in 0 position equipment located remotely
- Applications:
 - breaking of CMV (controlled mechanical ventilation motors, fixed or moving machines, air-conditioners)
- Can also be used as a:
 - general switch
 - emergency stop
- IP 65

Documentation

Catalogue pages & additional information

- [Description page \(p.177\)](#)


Installation instructions & related documents

- 0064C67-05
- 0064DP106_07