

CAT. N° 0 226 34


**FULL LOAD SWITCH UNIT WITH VISTOP - 125 A - 4P**

|                           |          |
|---------------------------|----------|
| Pack (number of units)    | 1        |
| Volume (dm <sup>3</sup> ) | 26,298   |
| Weight (g)                | 4 000,00 |

**Product characteristics**
**Full load switch units 32 to 160 A**

- Comprising:
  - IP 65 plastic box with transparent hinged cover equipped with a Vistop with side red handle, yellow front plate with N/C + N/O auxiliary contact
  - earth terminal (Viking 3)

**125 A - IK 07**

- Supplied with 2 cable glands 36P - ISO 50
- 4P
- Connection : 50 mm<sup>2</sup> flexible - 70 mm<sup>2</sup> rigid
- Earth terminal nominal capacity : 50 mm<sup>2</sup>

**General characteristics**
**Proximity switching 32 to 160 A**

- For on-load circuit breaking, isolation and locking in 0 position equipment located remotely
- Applications:
  - breaking of CMV (controlled mechanical ventilation motors, fixed or moving machines, air-conditioners)
- Can also be used as a:
  - general switch
  - emergency stop
- IP 65

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.177\)](#)


**Installation instructions & related documents**

- [0064DP108](#)