

CAT. N° 0 227 32


**FRONT EXTERNAL HANDLE - FOR VISTOP 63 TO 160 A**

|                           |        |
|---------------------------|--------|
| Pack (number of units)    | 1      |
| Volume (dm <sup>3</sup> ) | 1,63   |
| Weight (g)                | 511,00 |

**Product characteristics**
**Accessories**
**Front external handle for Vistop 63 to 160 A**

- Comprising: connection rod, bracket, self-adhesive drilling template, fixing accessories (including a seal to maintain the IP protection of enclosure up to IP 55) and locking mechanism to prevent opening of the door when the circuit is closed
- Door distance 35 to 470 mm

**General characteristics**
**Vistop™ isolating switches - 32 to 160 A**

- Safety switches for on-load circuit breaking by visible isolation of the contacts
- Double break type load switching with self cleaning contacts by rapid make and break movements
- Fixing on rail EN 60715 or screw fixing (only on rail for Vistop 63 A)
- Padlockable handle in open position: 1 to 3 padlocks Cat.No 0 227 97
- 2 versions for mounting on faceplate:
  - right side handle, supplied with seal to maintain the IP protection for the enclosures (up to IP 55), screws, self adhesive drilling template, extension rod (30 to 170 mm) for creating an external angle
  - direct front handle or external (for Vistop 63 to 160 A)

**Documentation**

**Catalogue pages & additional information**

- [Description page \(p.166\)](#)
- [Vistop™ isolating switches](#)


**Installation instructions & related documents**

- 0064W44-06