

REF . 0 239 50

**OSMOZ NON ILLUMINATED KEY SELECTOR SWITCH - 2 STAY-PUT POSITIONS 45°**

Emballage (nombre number of units )	1
Volume (dm <sup>3</sup> )	0,08
Poids (g)	45,00

**Caractéristiques du produit****Selector switches****With key**

- Black button
- 2 stay-put positions - 45°

**Caractéristiques générales****Osmoz control and signalling units: non-illuminated heads**

- Supplied with a fixing ring
- IP 69, IP 69K
- Conform to IEC 60947-5-1

**Documentation associée****Catalogue pages & additional information**

- [Description page \(p.351\)](#)
- [Technical page \(p.355\)](#)
- [Osmoz: control and signalling units](#)

**Agreements & certificates of conformity**

- [VERITAS \(BV\)-16400/D0 BV](#)
- [UL recogn cUL-NKCR8](#)
- [OC / CB-FR\\_714621](#)