

REF . 0 240 36



OSMOZ ILLUM STANDARD HANDLE SELECTOR SWITCH - 2 STAY-PUT POSITIONS (0-12H) - GREEN



Emballage (nombre number of units)	1
Volume (dm ³)	0,08
Poids (g)	20,00

Caractéristiques du produit

Selector switches

With standard handle

- Green
- Positions : 2 stay-put positions - 45°

Caractéristiques générales

Osmoz control and signalling units: illuminated heads

- Supplied with a fixing ring
- IP 66, IP 69K
- Conform to IEC 60947-5-1

Documentation associée

Catalogue pages & additional information

- [Description page \(p.352\)](#)
- [Technical page \(p.355\)](#)
- [Osmoz: control and signalling units](#)

Environmental product profile

- [LGRP-2015-327-V1-EN](#)

Agreements & certificates of conformity

- [VERITAS \(BV\)-16400/D0 BV](#)
- [UL recogn cUL-NKCR8](#)
- [OC / CB-FR_714621](#)