

CAT. N° 0 260 60



ELECTRONIC EARTH LEAKAGE MODULES - DPX/DPX-I 630 - MOUNTED UNDERNEATH - 3P - 400 A

Pack (number of units)	1
Volume (dm ³)	7
Weight (g)	2 484,00

Product characteristics

Earth leakage modules

- Can be fitted onto DPX³/DPX³-I 630
- Adjustable, sealable sensitivity: 0.03 - 0.3 - 1 - 3 A
- Adjustable, time delay: 0 - 0.3 - 1 - 3 s
- Test push-button
- Reset push-button
- Remote earth fault signalling contact
- Switch for mechanical tests (installation insulation test)
- Mounted underneath
- 230-500 V~

Standard

- 3P
- In : 400 A

General characteristics

DPX³ 630 - earth leakage modules

Documentation

Catalogue pages & additional information

- [Description page \(p.148\)](#)
- [DPX³ 160/250/630 & 1600](#)
- [DPX³ 630](#)

Installation & technical data

- [EXB19026_CA_DPX3_125HP250HP_630_1600EN](#)

Installation instructions & related documents

- [LE07066AC](#)

Agreements & certificates of conformity

- [CCC-2005010307161816](#)